For current pricing, please see our website.

Ø1.5" Mounting Posts

Stackable P-Series Posts

C1501
Mounting Post Clamp
(See Page 109)

PB1
Mounting Post Bases

P-Series Posts

Our Ø1.5" (Ø38.0 mm) solid stainless steel P-Series Posts are offered in heights ranging from 1" (25 mm) to 14" (350 mm). This design offers the ability to stack multiple mounting posts to achieve an array of lengths. Using a hex wrench (standard 3/16" or 5 mm balldriver) inserted through the side clearance hole, sufficient torque can be achieved to securely tighten stacked posts. Mounting spacers (shown below) are also available to provide greater flexibility in height.

ITEM #	LENGTH	METRIC ITEM #	LENGTH	$	£	€	RMB
P1	1.00"	P25/M	25 mm	$ 19.50	£ 14.04	€ 16,97	¥ 155.42
P1.5	1.50"	P30/M	30 mm	$ 22.00	£ 15.84	€ 19,14	¥ 175.34
P2	2.00"	P50/M	50 mm	$ 26.00	£ 18.72	€ 22,62	¥ 207.22
P3	3.00"	P75/M	75 mm	$ 33.00	£ 23.76	€ 28,71	¥ 263.01
P4	4.00"	P100/M	100 mm	$ 38.00	£ 27.36	€ 33,06	¥ 302.86
P5	5.00"	P125/M	125 mm	$ 44.00	£ 31.68	€ 38,28	¥ 350.68
P6	6.00"	P150/M	150 mm	$ 49.00	£ 35.28	€ 42,63	¥ 390.53
P8	8.00"	P200/M	200 mm	$ 54.00	£ 38.88	€ 46,98	¥ 430.38
P10	10.00"	P250/M	250 mm	$ 68.00	£ 48.96	€ 59,16	¥ 541.96
P14	14.00"	P350/M	350 mm	$ 88.00	£ 63.36	€ 76,56	¥ 701.36

Ø1.5" Mounting Post Spacers

Mounting post spacers, which enable in-between heights to be achieved, provide greater height flexibility when building support structures.

ITEM #	HEIGHT	METRIC ITEM #	HEIGHT	$	£	€	RMB
PS1	1/8"	PS5/M	5.0 mm	$ 8.20	£ 5.90	€ 7,13	¥ 65.35
PS2	1/4"	PS10/M	10.0 mm	$ 8.80	£ 6.34	€ 7,66	¥ 70.14
PS3	1/2"	PS15/M	15.0 mm	$ 9.80	£ 7.06	€ 8,53	¥ 78.11
PS4	3/4"	PS20/M	20.0 mm	$ 10.30	£ 7.42	€ 8,96	¥ 82.09

Pedestal Post Adapter

PF175
Post Sold Separately

PB4

The PB4 Pedestal Post Adapter is designed to thread onto the bottom of our P-Series Posts. This allows our heavy-duty PF175 Clamp to be used to position the post assembly conveniently on your optical bench.

ITEM #	METRIC ITEM #	$	£	€	RMB	DESCRIPTION
PB4	PB4/M	$ 12.40	£ 8.93	€ 10,79	¥ 98.83	P-Series Pedestal Base Adapter
PF175	PF175*	$ 16.80	£ 12.10	€ 14,62	¥ 133.90	P-Series Clamping Fork

*Universal Design Imperial and Metric Compatible

Mounting Post Bases

PB1
1/4" (M6) Counterbores



PB2
1/4"-20 (M6 x 1.0) Tapped Hole

PB1

The standard post base bolts directly onto P-Series posts. To mount on an optical bench, four 1/4" (M6) counterbored holes on 2.00" (50.0 mm) centers are provided.

PB2

The universal post base allows random placement of the P-Series post. The PB2 attaches to P-Series posts with a 1/4"-20 (M6 x 1.0) center-tapped hole.

ITEM #	METRIC ITEM #	SIZE	$	£	€	RMB
PB1	PB1*	Ø2.48" x 0.4"	$ 23.70	£ 17.06	€ 20,62	¥ 188.89
PB2	PB2/M	Ø2.40" x 1/2"	$ 26.80	£ 19.30	€ 23,32	¥ 213.60

*Universal Design is Imperial and Metric Compatible