

## ▼ CHAPTERS

Fiber Patch  
Cables

Bare Fiber

Fiber  
OptomechanicsFiber  
ComponentsTest and  
Measurement

## ▼ SECTIONS

FiberBench

FiberPorts

Fiber Launch  
Platforms

Fiber Adapters

## Rotation Mount



RCB


- Mount Filters or Polarizers up to 1 mm Thick and 14 mm in Diameter
- Ø4 mm Clear Aperture
- Optic Secured with Retaining Ring
- Magnetic Mount for Smooth, Continuous Rotation
- 360° Rotation
- 1.5° Measurement Precision

ITEM #	\$	£	€	RMB	DESCRIPTION
RCB	\$ 65.00	£ 46.80	€ 56,55	¥ 518.05	FiberBench Rotation Mount

## FiberBench Mounting Adapter

The FT-SM05 optics mount is designed to hold Ø1/2" optics while also maintaining the appropriate beam height when placed on a FiberBench or FiberTable. It features our standard SM05 thread (Ø0.535"-40).

- Holds Ø1/2" Optics up to 3.9 mm Thick
- Ø11 mm Clear Aperture
- Retaining Ring Included



FT-SM05

SM05RR Retaining  
Ring Included

ITEM #	\$	£	€	RMB	DESCRIPTION
FT-SM05	\$ 40.00	£ 28.80	€ 34,80	¥ 318.80	FiberBench Mounting Adapter for Ø1/2" Optics, Internal SM05 Threading

## Aperture Plates

- Mounts in FT-SM05 Ø1/2" Optic Mount
- Ø1.5 and Ø2.5 mm Apertures



AP1.5



AP2.5

Aperture plates are a useful tool for system alignment or to measure beam size. When the aperture plate is mounted into the above FT-SM05 mount, it can be used to establish an optical center line in a FiberBench/FiberTable system. It is also useful for blocking stray light or other unwanted light in an optical system.


ITEM #	\$	£	€	RMB	DESCRIPTION
AP1.5	\$ 10.00	£ 7.20	€ 8,70	¥ 79.70	Ø1.5 mm Alignment Aperture Plate
AP2.5	\$ 10.00	£ 7.20	€ 8,70	¥ 79.70	Ø2.5 mm Alignment Aperture Plate

## Static Mounting Platform



HCB

- Use for Static Mounting of Filters, Prisms, and Polarizers
- Approximately 1.5 mm from Beam Center Line to Top Surface
- Epoxy Optic to Mount




ITEM #	\$	£	€	RMB	DESCRIPTION
HCB	\$ 40.00	£ 28.80	€ 34,80	¥ 318.80	Static Mounting Platform for FiberBench

## Universal Mounting Base



UCB

- Used for Mounting Filters and Windows
- Non-Marring Delrin® Construction
- 14 mm Maximum Optic Thickness



Please refer to our website for complete models and drawings.

ITEM #	\$	£	€	RMB	DESCRIPTION
UCB	\$ 60.00	£ 43.20	€ 52,20	¥ 478.20	Universal Mounting Base for FiberBench